

GENERAL NOTES

ALL DIMENSIONS ARE IN MM.  
GENERAL TOLERANCE ON BUILDING ±5MM.

SERVICE REQUIREMENTS (BY OTHERS)


STEAM – SUPPLY TO BE BETWEEN 400 & 600 KPA AT 0.97 DRYNESS FACTOR, CHLORIDE FREE, COMPLETE WITH 32mm ISOLATING VALVE. AVERAGE STEAM CONSUMPTION APPROXIMATELY 70KG/HR. MAXIMUM FLOW RATE 120 KG/HR FOR 3 MINUTES.

WATER MAINS – SUPPLY TO BE CONSTANTLY BETWEEN 200 & 500 KPA, MAXIMUM TEMPERATURE 25°C, CHLORIDE FREE COMPLETE WITH 20MM ISOLATING VALVE & BACKFLOW PREVENTION TO AS 3500.1, AVERAGE WATER CONSUMPTION APPROXIMATELY 18 LITRES/MIN. MAXIMUM FLOW RATE 25 LITRES/MIN FOR 3 MINUTES.

NOTE! WATER CONSUMPTION CAN BE SIGNIFICANTLY REDUCED IF CHILLED WATER IS AVAILABLE.

POWER – 20 AMPS/PHASE, 415 VOLT COMPLETE WITH NEUTRAL & EARTH. ISOLATING SWITCH ON UNIT.

WASTE – ø50mm TO SEWER IN COMPLIANCE WITH AS 3500.2  
WASTE TEMPERATURE UP TO 100°C SHORT TERM.



# Athnertron

HOSPITAL EQUIPMENT  
COMMERCIAL KITCHEN EQUIPMENT  
AIR CONDITIONING & MECHANICAL SERVICES

Head Office, Melbourne Phone: 9497 2500  
Fax: 9497 1190

Adelaide Phone: 8262 9044 Brisbane Phone: 3277 1321  
Sydney Phone: 9679 8911 Perth Phone: 9249 6166  
Web: www.athnertrononline.net

**PROJECT NAME**

**MAIN TITLE**

STERILISER INSTALLATION

**SUB TITLE**

TSB 9

**SUB TITLE**

GORILLA SERIES

**LOCATION**

**ITEM**

**PRODUCTION ORDER**

--	--	--	--	--	--


**DRAWN**

H.R

DATE  
01/09/05

SCALE  
1:30

**APPROVED BY**



**STATUS**

<input type="checkbox"/> UNAPPROVED	<input type="checkbox"/> PENDING APPROVAL
<input type="checkbox"/> APPROVED BY CLIENT	<input type="checkbox"/> APPROVED FOR MANUFACTURE

**DRG**

SKETCH 1

**REV**